

DCU-2 Firmware Upgrade Notes

2/28/14

hgain DCU2 1b Id 022814.hex

Adds a CONTRAST control in the SETUP MENU.

Once installed the contrast can be adjusted for best viewing by:

1. Selecting MENU by pushing in the HEADING SET/MENU knob
2. Turn the knob to select item 10 CONTRAST and push the knob.
3. Turn the knob for best contrast. The range is 0 to 32 with the default of 14. Press the knob when the best contrast is selected.

Note the best contrast may not be the same setting for REV (White background and blue lettering).
As for NOR (blue background with white lettering).